

NEEDLE DETECTOR

HANDY TYPE

HN-35W / HN-30S

Antimicrobial



HN-35W

HN-30S

Updated detection function
Notice by light and buzzer
Always keep clean by antimicrobial processing

Features

- **φ0.8 mm steel ball is detected**
This new handy type needle detector can detect φ0.8mm steel ball and is good for a steel pin
- **Easy to use with clean**
New design and Antimicrobial processing, using long time with no stress
- **Detecting wider area (HN-35W)**
Unit surface is wider and easy to detect by Spot/Wider sensitivity select switch
- **Sensitivity select switch (HN-30S)**
The new handy type needle detector adopts Hi/Low sensitivity select switch
- **Battery save function**
Under stand by, the battery mode is changed to save mode automatically, which saves battery consumption. When take it in hand, the machine starts automatically. New designed detecting circuit cuts electric power consumption.
- **Large size LED lamp and buzzer.**
It's easy to check the detecting result by adapting large size LED lamp and buzzer.

Detects iron pieces such in
as broken needles
applied products.
■ Incompletion of detection
detected by the Conveyor
type needle detector or
needle detector.



**ISO 22196
for KOHKIN**

無機抗菌剤・線込
本体

JP0122538A0001X

Based on the results evaluated by ISO22196 method,
SIAA is displayed on products with quality control
and information disclosure according to Antimicro-
bial Product Technology Council guidelines.

Model	HN-35W	HN-30S
Detection Method	Magnetic induction	Magnetic induction
Detection Ability	φ0.8mm Sphere	Hi: φ0.8mm Sphere Low: φ1.0mm Sphere
Detection Area	Spot / Wide	
Alarm Method	Buzzer, LED lamp	Buzzer, LED lamp
Detecting Area	48mm(W)×93mm(D)	25mm(W)×50mm(D)
Power Supply	1.5V dry cell battery×2(AA)	1.5V dry cell battery×2(AA)
Dimension	56(W)×245(L)×67(H)mm	58(W)×195(L)×50(H)mm
Weight	300g	210g

※ Use non ferrous metal accessories for garments.

※ The specification is under standard test condition. We have no responsibility for needle chip, iron chip etc.
Come out after detection under non-standard condition.



HASHIMA CO., LTD.

■ **HEAD OFFICE** 7-6 RYOGI, Gifu-CITY, JAPAN
TEL: 81-58-247-8400 / 81-58-245-4501
FAX: 81-58-240-5775

■ **IBI FACTORY (JAPAN)**

TEL: 81-585-22-6678 FAX: 81-585-22-6699

■ **FACTORY : KUNSHAN (CHINA)**

TEL: 0512-57771838 FAX: 0512-57771848

■ **SINGAPORE OFFICE**

TEL: 65-62858131 FAX: 65-62858132

■ **INDIA OFFICE**

TEL: 91-80-4154-0315 FAX: 91-80-2559-2002

■ **BANGLADESH OFFICE**

TEL: 880-2-7913655 FAX: 880-2-7913099

■ **VIETNAM OFFICE**

TEL: 84-226-3555840 FAX: 84-226-3555841